



# HPL-N

## H38JA-100/DX 12PK

Standard High Pressure Mercury lamp

### Warnings and Safety

- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	542 [CCT of 4200K]
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	370
Chromaticity Coordinate Y (Nom)	370
Correlated Color Temperature (Nom)	3950 K
Luminous Efficacy (rated) (Nom)	42 lm/W
Operating and Electrical	
Power Consumption	100.0 W
Voltage (Nom)	130 V


Voltage (Nom)	130 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Coated glass
Bulb Material	Hard Glass
Bulb Shape	ED75 [ED 75mm]
Approval and Application	
Mercury (Hg) Content (Nom)	13.7 mg
Product Data	
Order product name	HPL-N 100W E39 HG 1SL/12
Full product name	H38JA-100/DX 12PK
Full product code	104667733713115

HPL-N

Order code	337139
Material Nr. (12NC)	928485500091
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677337131


Numerator - Packs per outer box	12
EAN/UPC - Case	50046677337136

Dimensional drawing



Product	D (max)	C (max)
HPL-N 100W E39 HG 1SL/12	76 mm	188 mm

Photometric data



Spectral Power Distribution Colour - HPL-N 100W E39 HG 1SL/12

