



# SON-T 高壓鈉燈

## SON-T 250W E E40 SL/12

高壓鈉燈，外層為透明管狀燈泡

### 产品数据

基本資訊	
接口	E40 [ E40]
操作位置	UNIVERSAL [ 任意]
至 5% 故障的使用時間 (標稱)	12000 h
至 20% 故障的使用時間 (標稱)	20000 h
至 50% 故障的使用時間 (標稱)	28000 h
系統說明	外部 接觸器 (E)
照明科技	
色碼	220 [ CCT of 2000K]
光通量 (額定) (最小)	25200 lm
光通量 (額定) (標稱)	28000 lm
流明維護量 2000 h (最低)	95 %
流明維護量 2000 h (標稱)	98 %
流明維護量 5000 h (最低)	92 %
流明維護量 5000 h (標稱)	96 %
相關色溫 (標稱)	2000 K
光效 (額定) (標稱)	110 lm/W
演色性指數 (最大)	25
演色性指數 (標稱)	-
運作和電氣	
Power (Rated) (Nom)	250.0 W
燈具電流 (EM) (標稱)	3 A
啟動供電電壓 (最大)	198 V
啟動峰值電壓 (最大)	2800 V

重新啟動時間 (最小) (最大)	120 s
啟動時間 (最大)	5 s
電壓 (最大)	115 V
電壓 (最小)	85 V
電壓 (標稱)	100 V
控制調光	
可調光	Yes
啟動時間 90% (最大)	5 min
機械和殼體	
燈泡表層	透明
接口資訊	鈉 [-]
應用	
能源效益標籤 (EEL)	A+
汞 (Hg) 含量 (標稱)	20.4 mg
能源消耗 kWh/1000 h	275 kWh
燈具設計要求	
燈泡溫度 (最大)	450 °C
接口溫度 (最大)	250 °C
產品參數	
完整產品碼	871829121288100
訂購產品名稱	SON-T 250W E E40 SL/12

## SON-T 高壓鈉燈


EAN/UPC - 產品	8718291212881
訂購代碼	928487200098
分子 - 各件數量	1
分子 - 每一外盒內件數	12

材質編號(12NC)	928487200098
淨重 (件)	0.137 kg

### 安全提示

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



### 二维绘图



SON-T 250W E40

Product	D (max)	O	L	C (max)
SON-T 250W E E40 SL/12	47 mm	66 mm	158 mm	255 mm


### 光度数据



LDPO\_SON-T-Spectral power distribution Colour

## SON-T 高壓鈉燈

### 壽命



LDLE\_SON-T\_0001-Life expectancy diagram

