

PHILIPS

Lighting



MSD Platinum (Touring/Stage)

MSD Platinum 20 RB UNP/24

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

Product data

General Information		Luminous Efficacy (rated) (Nom)	
Base	- [-]	47 lm/W	
Operating Position	Universal [Universal]	Operating and Electrical	
Main Application	Stage/Touring	Power (Rated) (Nom)	470 W
Life to 50% Failures (Nom)	1500 h	Voltage (Max)	110 V
System Description	Reflector E21.9 TCM	Voltage (Min)	85 V
Light Technical		Controls and Dimming	
Color Code	2	Dimmable	Yes
Initial lumen (Nom)	22400 lm	Mechanical and Housing	
Chromaticity Coordinate X (Max)	314	Cap-Base Information	na [-]
Chromaticity Coordinate X (Min)	280	Luminaire Design Requirements	
Chromaticity Coordinate X (Nom)	296	Bulb Temperature (Max)	900 °C
Chromaticity Coordinate Y (Max)	316	Pinch Temperature (Max)	350 °C
Chromaticity Coordinate Y (Min)	290		
Chromaticity Coordinate Y (Nom)	298		
Correlated Color Temperature (Nom)	8000 K		

MSD Platinum (Touring/Stage)


Product Data	
Order product name	MSD Platinum 20 RB UNP/24
EAN/UPC - Product	8718696684221
Order code	323733
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	24
Material Nr. (12NC)	928495205308
Net Weight (Piece)	136.600 g

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Dimensional drawing



Product	D (max)	O	C (max)
MSD Platinum 20 RB UNP/24	58.5 mm	1.2 mm	72 mm

MSD Platinum 20 RB

