



# MASTERColour CDM MW Eco

## MSTColour CDM-EP MW eco 230W/840 E40 CL

Ceramic metal halide lamps with clear tubular or coated ellipsoid outer bulb, tailor-made to replace and outperform quartz metal halide lamps on existing gear.

### Warnings and Safety

- For use with control gear designed for high pressure mercury or high-pressure sodium lamps with external ignitor
- A lamp breaking is extremely unlikely to have an impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Warm restart time can be up to 15 minutes; T15 ignitors therefore advised.

### Product data


General Information		Operating and Electrical	
Cap-Base	E40 [E40]	Power Consumption	225 W
Operating Position	UNIVERSAL [Any or Universal (U)]	Voltage (Nom)	123 V
Life to 50% Failures (Nom)	20,000 hour(s)	Voltage (Nom)	123 V
Light Technical		Mechanical and Housing	
Color Code	840 [CCT of 4000K]	Bulb Finish	Clear
Luminous Flux (Min)	18,900 lm	Bulb Material	Hard Glass
Color Designation	Cool White (CW)	Bulb Shape	B90 [B 90mm]
Chromaticity Coordinate X (Nom)	379		
Chromaticity Coordinate Y (Nom)	380		
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (Rated) (Min)	84 lm/W		
Luminous Efficacy (rated) (Nom)	93 lm/W		
Color rendering index (CRI)	87		
		Approval and Application	
		Energy Efficiency Class	F
		Mercury (Hg) Content (Nom)	27 mg
		Energy Consumption kWh/1000 h	248 kWh

# MASTERC colour CDM MW Eco

Product Data	
Order product name	MSTColour CDM-EP MW eco 230W/840 E40 CL
Full product name	MSTColour CDM-EP MW eco 230W/840 E40 CL
Full product code	871869673479700
Order code	928495309891
Material Nr. (12NC)	928495309891

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696734797
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696734803

## Dimensional drawing



Product	D (max)	C (max)
MSTColour CDM-EP MW eco 230W/840 E40 CL	91 mm	215 mm

