

MSD Platinum (Touring/Stage)

MSD Platinum 400L Flex 1CT/8

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



Product data

General Information		Operating and Electrical	
Operating Position	UNIVERSAL [Any or Universal (U)]	Power Consumption	470 W
Life to 50% Failures (Nom)	2,000 hour(s)		
Light Technical		Controls and Dimming	
Color Code	2	Dimmable	Yes
Luminous Flux	24,000 lm		
Chromaticity Coordinate X (Nom)	297		
Chromaticity Coordinate Y (Nom)	303		
Correlated Color Temperature (Nom)	8000 K		
Arc Length O (Nom)	1.2 mm		
		Product Data	
		Order product name	MSD Platinum 400L Flex 1CT/8
		Full product name	MSD Platinum 400L Flex 1CT/8
		Full product code	871869965196100
		Order code	928496405314
		Material Nr. (12NC)	928496405314
		Numerator - Quantity Per Pack	1

MSD Platinum (Touring/Stage)


EAN/UPC - Product/Case	8718699651961
Numerator - Packs per outer box	8
EAN/UPC - Case	8718699651978

Dimensional drawing



Product	D (max)	O	C (max)
MSD Platinum 400L Flex 1CT/8	54.5 mm	1.2 mm	60 mm

Photometric data



Spectral Power Distribution Colour - MSD Platinum 400L Flex 1CT/8

