



Ceramalux ALTO

C70S62/D ALTO PH 12PK

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)
Light Technical	
Chromaticity Coordinate X (Nom)	524
Chromaticity Coordinate Y (Nom)	425
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	75.7 lm/W
Luminous Efficacy (rated) (Nom)	85.7 lm/W
Color rendering index (CRI)	21
Operating and Electrical	
Lamp Current (Nom)	1.6 A
Voltage (Nom)	52 V
Voltage (Nom)	52 V
Mechanical and Housing	
Bulb Finish	Coated glass

Bulb Material	Hard Glass
Bulb Shape	ED-23 1/2
Approval and Application	
Mercury (Hg) Content (Max)	17 mg
Product Data	
Order product name	C70S62/D ALTO PH 12PK
Full product name	C70S62/D ALTO PH 12PK
Order code	332254
Material Nr. (12NC)	928601107602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677332259
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677332254

Ceramalux ALTO

Dimensional drawing

Product
C70S62/D ALTO PH 12PK

