



Switch Start Metal Halide Protected

MH175/U/M 3PK

An efficient, protected "O" rated lighting solution that is suitable for open-rated fixtures. Ideal for both indoor and outdoor applications.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Main Application	General Lighting (G)
Life to 50% Failures (Nom)	10000 h
ANSI Code HID	M57/E
Footnotes HID 1	Requires a ballast specified or approved for Philips metal halide lamps, or one that is designed to operate all popular brands of metal halide lamps. 1000W types will operate from H36 conventional lag type ballast for Mercury Vapor lamps at ambient temperatures of 50 degrees F or higher. 1000W types must not be operated at 1500W. (377)
Footnotes HID 2	Rated life: Vertical +/- 15 degrees. Other positions 75% of vertical life. (385)
Footnotes HID 3	Vertical lumens. Horizontal lumens 6%–10% lower. (393)
Light Technical	
Color Code	640 [CCT of 4000K]
Luminous Flux (Rated) (Nom)	14000 lm
Color Designation	Cool White (CW)

Design Mean Lumens	9100 lm
Chromaticity Coordinate X (Nom)	0.385
Chromaticity Coordinate Y (Nom)	0.390
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (Rated) (Min)	70 lm/W
Luminous Efficacy (rated) (Nom)	80 lm/W
Color Rendering Index (Nom)	65
Operating and Electrical	
Lamp Current (Nom)	1.5 A
Ignition Supply Voltage (Min)	350 V
Re-Ignition Time (Min) (Max)	15 min
Ignition Time (Max)	120 s
Voltage (Max)	147 V
Voltage (Min)	117 V
Voltage (Nom)	132 V
Mechanical and Housing	
Bulb Finish	Clear
Cap-Base Information	Brass Cap
Bulb Material	Hard Glass

Switch Start Metal Halide Protected

Approval and Application

Energy Saving Product	Not Applicable
Mercury (Hg) Content (Max)	24.0 mg

UV

Pet (Niosh) (Nom)	147.03 h/500lx
Damage Factor D/fc (Nom)	0.42

Luminaire Design Requirements

Bulb Temperature (Max)	450 °C
Cap-Base Temperature (Max)	210 °C

Product Data


Order product name	MH175/U/M 3PK
EAN/UPC - Product	046677460778
Order code	928601122312
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	3
Material Nr. (12NC)	928601122312
Net Weight (Piece)	70.000 g

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Dimensional drawing

Product	D	C (max)
MH175/U/M 3PK	2.125 in	5.438 in



MH R 175W/640 E26 BD17 U

