



Ceramalux ALTO

C400S51/ALTO 12PK

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	Universal [Universal]
Main Application	General and Street Lighting
ANSI Code HID	S51
Features	ALTO® (ALTO)

Light Technical	
Luminous Flux (Rated) (Min)	45000 lm
Luminous Flux (Rated) (Nom)	50000 lm
Photosynthetic Photon Flux (PPF)	595 µmol/s
Design Mean Lumens	45000 lm
Chromaticity Coordinate X (Nom)	515
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	112.5 lm/W
Luminous Efficacy (rated) (Nom)	125 lm/W
Color Rendering Index (Nom)	20

Operating and Electrical	
Lamp Current (Nom)	4.6 A
Ignition Supply Voltage (Max)	198 V
Re-Ignition Time (Min) (Max)	1 min
Ignition Time (Max)	5 s
Voltage (Max)	115 V

Voltage (Min)	84 V
Voltage (Nom)	100 V

Mechanical and Housing	
Bulb Finish	Clear (CL)
Cap-Base Information	Brass [Brass Cap]
Bulb Material	Hard Glass

Approval and Application	
Picogram Per Lumen Hour	26.4 pg/lm.h
Mercury (Hg) Content (Max)	23.5 mg

UV	
Pet (Niosh) (Nom)	353 h/500lx
Damage Factor D/fc (Nom)	0.03

Luminaire Design Requirements	
Bulb Temperature (Max)	400 °C
Cap-Base Temperature (Max)	210 °C

Product Data	
Order product name	SON 400W E39 ED58 CL SL/12
EAN/UPC - Product	046677467371
Order code	467373
Numerator - Quantity Per Pack	1


Ceramalux ALTO

Numerator - Packs per outer box	12
Material Nr. (12NC)	928601139391
Net Weight (Piece)	165.000 g

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Dimensional drawing



Product

SON 400W E39 ED58 CL SL/12

HPS 400W E39 ED18 U ALTO

