



Ceramalux ALTO

C70S62/ALTO 12PK

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	Universal [Universal]
Main Application	General and Street Lighting
ANSI Code HID	S62
Features	ALTO® (ALTO)

Light Technical	
Luminous Flux (Rated) (Min)	6100 lm
Luminous Flux (Rated) (Nom)	6800 lm
Design Mean Lumens	5670 lm
Chromaticity Coordinate X (Nom)	522
Chromaticity Coordinate Y (Nom)	425
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	87.4 lm/W
Luminous Efficacy (rated) (Nom)	97 lm/W
Color Rendering Index (Nom)	13

Operating and Electrical	
Lamp Current (Nom)	1.6 A
Ignition Supply Voltage (Max)	110 V
Re-Ignition Time (Min) (Max)	2 min
Ignition Time (Max)	5 s
Voltage (Max)	60 V
Voltage (Min)	44 V

Voltage (Nom)	52 V
---------------	------

Mechanical and Housing	
Bulb Finish	CL [Clear (CL)]
Cap-Base Information	Brass [Brass Base]
Bulb Material	Hard Glass

Approval and Application	
Mercury (Hg) Content (Max)	17 mg

Luminaire Design Requirements	
Bulb Temperature (Max)	400 °C
Cap-Base Temperature (Max)	210 °C


Product Data	
Order product name	SON 70W E39 ED75 CL SL/12
EAN/UPC - Product	046677467258
Order code	467258
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928601139990
Net Weight (Piece)	108.000 g

Ceramalux ALTO

Dimensional drawing

Product

SON 70W E39 ED75 CL SL/12



HPS 70W E39 ED23 1/2 U ALTO

