



Ceramalux Non-ALTO

C70S62/M PH 12PK

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Main Application	General Lighting (G)
ANSI Code HID	S62
Footnotes HID 1	For use in fixtures which do not redirect a substantial portion of the energy toward the arc tube; otherwise very early failure is anticipated. (376)

Light Technical	
Luminous Flux (Rated) (Min)	5900 lm
Luminous Flux (Rated) (Nom)	6500 lm
Lumen Maintenance 10000 h (Nom)	70 %
Design Mean Lumens	5850 lm
Chromaticity Coordinate X (Nom)	522
Chromaticity Coordinate Y (Nom)	425
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	84 lm/W
Luminous Efficacy (rated) (Nom)	92 lm/W
Color Rendering Index (Nom)	13

Operating and Electrical	
Lamp Current (Nom)	1.6 A
Ignition Supply Voltage (Max)	110 V

Re-Ignition Time (Min) (Max)	2 min
Ignition Time (Max)	5 s
Voltage (Max)	60 V
Voltage (Min)	44 V
Voltage (Nom)	52 V

Mechanical and Housing	
Bulb Finish	Clear (CL)
Cap-Base Information	Brass [Brass Cap]
Bulb Material	Soft Glass

Approval and Application	
Mercury (Hg) Content (Max)	17 mg

Luminaire Design Requirements	
Bulb Temperature (Max)	400 °C
Cap-Base Temperature (Max)	190 °C

Product Data	
Order product name	C70S62/M PH 12PK
EAN/UPC - Product	046677467289
Order code	467282
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928601144190

Ceramalux Non-ALTO


Net Weight (Piece)	61.000 g
--------------------	----------

Warnings and Safety

· Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Dimensional drawing

Product	D	C (max)
C70S62/M PH 12PK	2.125 in	5.438 in



HPS R S62 70W E26 BD17 U

