



Ceramalux Non-ALTO

35W BD17 HP SODIUM HID CLR

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	537
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	59 lm/W
Luminous Efficacy (rated) (Nom)	64 lm/W
Color rendering index (CRI)	7.5
Operating and Electrical	
Power Consumption	35.1 W
Lamp Current (Nom)	0.83 A
Voltage (Nom)	55 V
Voltage (Nom)	55 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	BD17
Approval and Application	
Mercury (Hg) Content (Nom)	16.8 mg
Product Data	
Order product name	35W BD17 HP SODIUM HID CLR
Full product name	35W BD17 HP SODIUM HID CLR
Order code	928601144314
Material Nr. (12NC)	928601144314
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677460853
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677460858

Ceramalux Non-ALTO

Dimensional drawing

Product	D	C (max)
35W BD17 HP SODIUM HID CLR	55 mm	138 mm

