



Ceramalux Non-ALTO

C35S76/M 12PK

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Main Application	General Lighting (G)
ANSI Code HID	S76
Light Technical	
Luminous Flux (Rated) (Min)	2050 lm
Luminous Flux (Rated) (Nom)	2250 lm
Lumen Maintenance 10000 h (Nom)	93 %
Lumen Maintenance 20000 h	82 %
Design Mean Lumens	2025 lm
Chromaticity Coordinate X (Nom)	537
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	59 lm/W
Luminous Efficacy (rated) (Nom)	63 lm/W
Color Rendering Index (Nom)	7.5
Operating and Electrical	
Lamp Current (Nom)	0.83 A
Ignition Supply Voltage (Max)	110 V
Re-Ignition Time (Min) (Max)	5 min
Ignition Time (Max)	5 s
Voltage (Max)	62 V

Voltage (Min)	45 V
Voltage (Nom)	55 V

Mechanical and Housing	
Bulb Finish	Clear (CL)
Cap-Base Information	Brass [Brass Cap]
Bulb Material	Hard Glass

Approval and Application	
Mercury (Hg) Content (Nom)	16.8 mg

Luminaire Design Requirements	
Bulb Temperature (Max)	400 °C
Cap-Base Temperature (Max)	190 °C

Product Data	
Order product name	C35S76/M 12PK
EAN/UPC - Product	046677467296
Order code	467290
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928601144390
Net Weight (Piece)	60.000 g


Ceramalux Non-ALTO

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Dimensional drawing

Product	D	C (max)
C35S76/M 12PK	2.125 in	5.438 in



HPS R 35W E26 BD17 U

