



Ceramalux Non-ALTO

C35S76/M 12PK

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	537
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	59 lm/W
Luminous Efficacy (rated) (Nom)	64 lm/W
Color rendering index (CRI)	7.5
Operating and Electrical	
Power Consumption	35.1 W
Lamp Current (Nom)	0.83 A
Voltage (Nom)	55 V
Voltage (Nom)	55 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	BD17

Approval and Application

Mercury (Hg) Content (Nom)	16.8 mg
----------------------------	---------

Product Data

Order product name	C35S76/M 12PK
Full product name	C35S76/M 12PK
Order code	467290
Material Nr. (12NC)	928601144390
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677467296
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677467291

Ceramalux Non-ALTO

Dimensional drawing

Product	D	C (max)
C35S76/M 12PK	55 mm	138 mm

