



Ceramalux Non-ALTO

SON 150W E26 BD54 CL SLV/12

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	514
Chromaticity Coordinate Y (Nom)	424
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	96 lm/W
Luminous Efficacy (rated) (Nom)	106 lm/W
Color rendering index (CRI)	17
Operating and Electrical	
Power Consumption	150.6 W
Lamp Current (Nom)	3.2 A
Voltage (Nom)	55 V
Voltage (Nom)	55 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	BD17
Approval and Application	
Mercury (Hg) Content (Max)	17 mg
Product Data	
Order product name	SON 150W E26 BD54 CL SLV/12
Full product name	SON 150W E26 BD54 CL SLV/12
Order code	928601147404
Material Nr. (12NC)	928601147404
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677303471
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677303476

Ceramalux Non-ALTO

Dimensional drawing

Product	D	C (max)
SON 150W E26 BD54 CL SLV/12	55 mm	145 mm

