



Switch Start Metal Halide Standard

MH400/U/ED28 3PK

High performance, Long life and Superior light quality. A compact, energy efficient metal halide lamp that provides crisp, sparkling light with long life and high efficiency.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA: 21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	E39 [Single Contact Mogul Screw]	90 lm/W	
Operating Position	UNIVERSAL [Any or Universal (U)]	Color rendering index (CRI)	
Life to 50% Failures (Nom)	20,000 hour(s)	57	
Light Technical		Operating and Electrical	
Color Code	640 [CCT of 4000K]	Power Consumption	400 W
Color Designation	Cool White (CW)	Lamp Current (Nom)	3.25 A
Chromaticity Coordinate X (Nom)	0.390	Voltage (Nom)	135 V
Chromaticity Coordinate Y (Nom)	0.400	Voltage (Nom)	135 V
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing	
Luminous Efficacy (Rated) (Min)	80 lm/W	Bulb Finish	Clear
		Bulb Material	Hard Glass

Switch Start Metal Halide Standard

Bulb Shape	ED28
------------	------

Approval and Application


Energy Saving Product	Not Applicable
Mercury (Hg) Content (Max)	52.0 mg

Product Data

Order product name	MH400/U/ED28 3PK
Full product name	MH400/U/ED28 3PK

Order code	140848
Material Nr. (12NC)	928601151304
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677253677
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677140842

Dimensional drawing



Product	D	C (max)
MH400/U/ED28 3PK	3.5 inch	8.313 inch

