



Pulse Start Metal Halide Protected

MP350/BU/PS 6PK

Philips Protected Pulse Start Metal Halide “O” Rated Lamps are a better alternative to the standard switch start metal halide.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data

General Information	
Cap-Base	EX39 [Exclusionary Mogul Screw]
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]
Life to 50% Failures (Nom)	20,000 hour(s)

Light Technical	
Color Code	640 [CCT of 4000K]
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	390
Chromaticity Coordinate Y (Nom)	395
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (Rated) (Min)	87.4 lm/W
Luminous Efficacy (rated) (Nom)	97 lm/W
Color rendering index (CRI)	64

Operating and Electrical	
Lamp Current (Nom)	2.83 A
Voltage (Nom)	135 V
Voltage (Nom)	135 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED37

Approval and Application	
Mercury (Hg) Content (Max)	43.5 mg

Product Data	
Order product name	MP350/BU/PS 6PK
Full product name	MP350/BU/PS 6PK

Pulse Start Metal Halide Protected

Order code	391011
Material Nr. (12NC)	928601159402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677391010

Numerator - Packs per outer box	6
EAN/UPC - Case	50046677391015

Dimensional drawing

Product	D	C (max)
MP350/BU/PS 6PK	4.625 inch	11.5 inch

