



# MasterColor CDM ED17 Standard

## MHC150/U/M/3K ALTO 12PK

Energy savings without changing a ballast!. A high-efficiency enclosed E-rated CDM lighting solution that provides energy savings without compromising light quality.

### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)
Life to 50% Failures (Nom)	16,000 hour(s)
Light Technical	
Color Code	830 [CCT of 3000K]
Color Designation	White (WH)
Chromaticity Coordinate X (Nom)	436
Chromaticity Coordinate Y (Nom)	393
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (Rated) (Min)	89 lm/W


Luminous Efficacy (rated) (Nom)	95 lm/W
Color rendering index (CRI)	90
Operating and Electrical	
Lamp Current (Nom)	1.8 A
Voltage (Nom)	95 V
Voltage (Nom)	95 V
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED17

MasterColor CDM ED17 Standard

Approval and Application	
Mercury (Hg) Content (Max)	15 mg
Product Data	
Order product name	MHC150/U/M/3K ALTO 12PK
Full product name	MHC150/U/M/3K ALTO 12PK
Order code	130229


Material Nr. (12NC)	928601170301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677130220
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677130225

Dimensional drawing



Product	D	C (max)
MHC150/U/M/3K ALTO 12PK	2.125 inch	5.438 inch

Lifetime



Life Expectancy Diagram - MHC150/U/M/3K ALTO 12PK

