



Energy Advantage CDM Lamps with Allstart Technology

CDM330/V/O/4K/EA/LL Allstart

Philips Energy Advantage CDM lamps with AllStart Technology is a high-efficiency protected “O” rated CDM lighting solution that provides energy savings without compromising light quality.

Warnings and Safety

- R "WARNING:These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data


General Information		Chromaticity Coordinate Y (Nom) 0.384	
Cap-Base	EX39 [Exclusionary Mogul Screw]	Luminous Efficacy (Rated) (Min)	91 lm/W
Operating Position	VBU/VBD20 [base up/base down +/- 20 degrees]	Luminous Efficacy (rated) (Nom)	100 lm/W
Features	ENERGYADVANTAGELONGL [Energy Advantage Long Life Allstart]	Color rendering index (CRI)	90
Life to 50% Failures (Nom)	36,000 hour(s)	Operating and Electrical	
Light Technical		Lamp Current (Nom)	3.02 A
Color Code	940 [CCT of 4000K]	Voltage (Nom)	130 V
Color Designation	4000 Kelvin	Voltage (Nom)	130 V
Saturated Red (R9)	50	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	0.381	Bulb Finish	Clear

Energy Advantage CDM Lamps with Allstart Technology

Bulb Shape	ED37
Approval and Application	
Mercury (Hg) Content (Max)	50 mg
Product Data	
Order product name	CDM330/V/O/4K/EA/LL Allstart
Order code	928601174801

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	928601174801
Full product name	CDM330/V/O/4K/EA/LL Allstart
EAN/UPC - Case	50046677421774
EAN/UPC - Product/Case	046677421779

Dimensional drawing



Product	D	D	L (max)	L	C
CDM330/V/O/4K/EA/LL Allstart	4.65 inch	118 mm	184 mm	178 mm	11.5 inch

