



# MasterColor CDM ED17 Protected Elite 4200K

## MHC70/C/U/MP/4K ELITE

MasterColor Elite Protected Ceramic Metal Halide ED-17 4200K Lamps provide excellent lumen maintenance and outstanding performance over time in a protected lamp.

### Product data

General Information		Light Technical	
Base	E26 [ Single Contact Medium Screw]	Chromaticity Coordinate Y (Max)	0.369
Operating Position	Universal [ Universal]	Chromaticity Coordinate Y (Min)	0.357
Main Application	General Lighting (G)	Chromaticity Coordinate Y (Nom)	0.363
Life to 50% Failures (Nom)	20000 h	Correlated Color Temperature (Nom)	4000 K
ANSI Code HID	C98/O	Luminous Efficacy (Rated) (Min)	80 lm/W
Features	ELITE	Luminous Efficacy (rated) (Nom)	84 lm/W
		Color Rendering Index (Min)	87
		Color Rendering Index (Nom)	90
Light Technical		Operating and Electrical	
Color Code	940 [ CCT of 4000K]	Lamp Current (Nom)	0.9 A
Luminous Flux (Rated) (Min)	5400 lm	Ignition Supply Voltage (Min)	235 V
Luminous Flux (Rated) (Nom)	5900 lm	Re-Ignition Time (Min) (Max)	8 min
Color Designation	Cool White (CW)	Ignition Time (Max)	10 s
Lumen Maintenance - 40% Life	80 %	Voltage (Max)	115 V
Lumen Maintenance - 10% Life	90 %	Voltage (Min)	95 V
Design Mean Lumens	4720 lm	Voltage (Nom)	100 V
Chromaticity Coordinate X (Max)	0.391		
Chromaticity Coordinate X (Min)	0.373		
Chromaticity Coordinate X (Nom)	0.382		

# MasterColor CDM ED17 Protected Elite 4200K


Mechanical and Housing	
Bulb Finish	Coated [ Coated glass (CO)]
Cap-Base Information	Brass [ Brass Cap]
Bulb Material	Hard Glass
Approval and Application	
Picogram Per Lumen Hour	79 pg/lm.h
Mercury (Hg) Content (Max)	7.1 mg
UV	
Pet (Niosh) (Nom)	347 h/500lx
Damage Factor D/fc (Nom)	0.28
Luminaire Design Requirements	
Bulb Temperature (Max)	400 °C

Cap-Base Temperature (Max)	190 °C
Product Data	
Order product name	MHC70/C/U/MP/4K ELITE
EAN/UPC - Product	046677429973
Order code	429976
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928601178001
Net Weight (Piece)	0.001 kg

## Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- WARNING: The arc-tube of metal halide lamps are designed to operate under high pressure and at temperatures up to 1000°C and can unexpectedly rupture due to internal or external factors such as a ballast failure or misapplication. If the arc-tube ruptures for any reason, the outer bulb may break and pieces of extremely hot glass might be discharged into the surrounding environment. If such a rupture were to happen, THERE IS A RISK OF PERSONAL INJURY, PROPERTY DAMAGE, BURNS AND FIRE. These lamps are designed to retain all the glass particles, should an arc tube rupture occur. The following operating instructions are recommended to minimize the occurrences.
- The arc-tube of metal halide lamps are designed to operate under high pressure and at temperatures up to 1000°C and can unexpectedly rupture due to internal or external factors such as a ballast failure or misapplication. If the arc-tube ruptures for any reason, the outer bulb may break and pieces of extremely hot glass might be discharged into the surrounding environment. If such a rupture were to happen, THERE IS A RISK OF PERSONAL INJURY, PROPERTY DAMAGE, BURNS AND FIRE. These lamps are designed to retain all the glass particles, should an arc tube rupture occur. The following operating instructions are recommended to minimize the occurrences.
- RELAMP FIXTURES AT OR BEFORE THE END OF RATED LIFE. Allowing lamps to operate until they fail is not advised and may increase the possibility of inner arc tube rupture.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

## Dimensional drawing



Product	D	C (max)
MHC70/C/U/MP/4K ELITE	2.125 in	5.438 in

MHC P 70W/940 E26 ED17P CO U ELITE

## MasterColor CDM ED17 Protected Elite 4200K

