



# MasterColor CDM ED17 Protected Elite 4200K

## MHC100/U/MP/4K ELITE

MasterColor Elite Protected Ceramic Metal Halide ED-17 4200K Lamps provide excellent lumen maintenance and outstanding performance over time in a protected lamp.

### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA: 21 CFR 1040.30 Canada: SOR/DORS/80-381)
- WARNING: The arc-tube of metal halide lamps are designed to operate under high pressure and at temperatures up to 1000°C and can unexpectedly rupture due to internal or external factors such as a ballast failure or misapplication. If the arc-tube ruptures for any reason, the outer bulb may break and pieces of extremely hot glass might be discharged into the surrounding environment. If such a rupture were to happen, THERE IS A RISK OF PERSONAL INJURY, PROPERTY DAMAGE, BURNS AND FIRE. These lamps are designed to retain all the glass particles, should an arc tube rupture occur. The following operating instructions are recommended to minimize the occurrences.
- The arc-tube of metal halide lamps are designed to operate under high pressure and at temperatures up to 1000°C and can unexpectedly rupture due to internal or external factors such as a ballast failure or misapplication. If the arc-tube ruptures for any reason, the outer bulb may break and pieces of extremely hot glass might be discharged into the surrounding environment. If such a rupture were to happen, THERE IS A RISK OF PERSONAL INJURY, PROPERTY DAMAGE, BURNS AND FIRE. These lamps are designed to retain all the glass particles, should an arc tube rupture occur. The following operating instructions are recommended to minimize the occurrences.
- RELAMP FIXTURES AT OR BEFORE THE END OF RATED LIFE. Allowing lamps to operate until they fail is not advised and may increase the possibility of inner arc tube rupture.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

# MasterColor CDM ED17 Protected Elite 4200K

## Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
Operating Position	Universal [ Universal]
Main Application	General Lighting (G)
Life to 50% Failures (Nom)	20000 h
ANSI Code HID	C90/O
Features	ELITE

Light Technical	
Color Code	940 [ CCT of 4000K]
Luminous Flux (Rated) (Min)	8500 lm
Luminous Flux (Rated) (Nom)	9400 lm
Color Designation	Cool White (CW)
Lumen Maintenance - 40% Life	80 %
Lumen Maintenance - 10% Life	90 %
Design Mean Lumens	7520 lm
Chromaticity Coordinate X (Max)	0.391
Chromaticity Coordinate X (Min)	0.373
Chromaticity Coordinate X (Nom)	0.382
Chromaticity Coordinate Y (Max)	0.377
Chromaticity Coordinate Y (Min)	0.362
Chromaticity Coordinate Y (Nom)	0.371
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (Rated) (Min)	91 lm/W
Luminous Efficacy (rated) (Nom)	94 lm/W
Color Rendering Index (Min)	87
Color Rendering Index (Nom)	90

Operating and Electrical	
Lamp Current (Nom)	1.1 A
Ignition Supply Voltage (Min)	235 V
Re-Ignition Time (Min) (Max)	10 min

Ignition Time (Max)	10 s
Voltage (Max)	118 V
Voltage (Min)	93 V
Voltage (Nom)	103 V

Mechanical and Housing	
Bulb Finish	Clear
Cap-Base Information	Brass [ Brass Cap]
Bulb Material	Hard Glass


Approval and Application	
Picogram Per Lumen Hour	68 pg/lm.h
Mercury (Hg) Content (Max)	10.3 mg

UV	
Pet (Niosh) (Nom)	387 h/500lx
Damage Factor D/fc (Nom)	0.28

Luminaire Design Requirements	
Bulb Temperature (Max)	400 °C
Cap-Base Temperature (Max)	190 °C

Product Data	
Order product name	MHC100/U/MP/4K ELITE
EAN/UPC - Product	046677429935
Order code	429936
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928601178101
Net Weight (Piece)	0.070 kg

## Dimensional drawing



MHC P 100W/940 E26 ED17P CL U ELITE

Product	D	C (max)
MHC100/U/MP/4K ELITE	2.125 in	5.438 in

## MasterColor CDM ED17 Protected Elite 4200K

