



MASTER LEDbulb

MAS LEDBulb D 7-40W E27 827 A60

The MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. They are particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimizes maintenance cost without any compromise on light quality. They can be used together with most leading-edge dimmers, enabling further efficiencies while helping to create the desired atmosphere.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime (nom.)	25000 h
Switching cycle	50000X
Technical type	7-40W
Light Technical	
Colour code	827 [CCT of 2,700 K]
Luminous flux (nom.)	470 lm
Luminous flux (rated) (nom.)	470 lm
Colour designation	Warm White (WW)
Correlated colour temperature (nom.)	2700 K
Luminous efficacy (rated) (nom.)	67.14 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	7 W
Lamp current (nom.)	44 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	7 kWh

MASTER LEDbulb


Product Data	
Full product code	871829167196100
Order product name	MAS LEDBulb D 7-40W E27 827 A60
EAN/UPC – product	8718291671961
Order code	67196100
Numerator – quantity per pack	1

Numerator – packs per outer box	6
Material no. (12NC)	929000247902
Net weight (piece)	0.134 kg

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights


Dimensional drawing



LED D 7-40W E27 827 A60

Product	D	C
MAS LEDBulb D 7-40W E27 827 A60	61.5 mm	109.6 mm

Photometric data



MASTER LEDbulb

