



MASTER LEDspot PAR

MAS LEDspot D 9.5-75W 827 PAR30S 25D

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on.

Product data

| General Information | |
|---------------------------------------|--------------------|
| Cap-Base | E27 [E27] |
| Nominal lifetime | 40,000 hour(s) |
| Switching Cycle | 50,000 |
| Lighting Technology | LED |
| EU RoHS compliant | Yes |
| Light Technical | |
| Color Code | 827 [CCT of 2700K] |
| Beam Angle (Nom) | 25 degree(s) |
| Luminous Flux | 650 lm |
| Luminous Intensity (Nom) | 3,500 cd |
| Color Designation | Warm White (WW) |
| Correlated Color Temperature (Nom) | 2700 K |
| Luminous Efficacy (rated) (Nom) | 68.42 lm/W |
| Color Consistency | <6 |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Luminous Flux in 90° Cone (Rated) | 650 lm |
| Operating and Electrical | |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |


| Power Consumption | 9.5 W |
|-------------------------------|--------------------------------------|
| Lamp Current (Nom) | 46 mA |
| Wattage Equivalent | 75 W |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction) | 0.9 |
| Voltage (Nom) | 220-240 V |
| Controls and Dimming | |
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Shape | PAR30S [PAR 3.75 inch/95mm Short] |
| Approval and Application | |
| Suitable For Accent Lighting | Yes |
| Energy Consumption kWh/1000 h | 10 kWh |
| EyeComfort | Yes |
| Product Data | |
| Order product name | MAS LEDspot D 9.5-75W 827 PAR30S 25D |
| Full product name | MAS LEDspot D 9.5-75W 827 PAR30S 25D |
| Full product code | 871829171434700 |

MASTER LEDspot PAR

| | |
|-------------------------------|---------------|
| Order code | 929000258802 |
| Material Nr. (12NC) | 929000258802 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718291714347 |


| | |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8718291714354 |

Dimensional drawing



| Product | D | C |
|--------------------------------------|-------|---------|
| MAS LEDspot D 9.5-75W 827 PAR30S 25D | 92 mm | 94.1 mm |

Photometric data



Light Distribution Diagram - MAS LEDspot D 9.5-75W 827 PAR30S 25D

