



MR16/GU10/PAR16

7MR16/F36 3000 DIM HO

Philips MR16 Dimmable LED Lamps provide ambient level light to illuminate hard to maintain applications. Increased transformer compatability allows for operation on a wider range of transformers. Available in dimmable and non-dimmable versions, these lamps are ideal for track and open recessed fixtures in retail, hospitality and residential spaces.

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Nominal lifetime	40,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	510 lm
Luminous Intensity (Nom)	1,350 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	72.86 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	470 lm
Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	7 W
Lamp Current (Nom)	715 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.8
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	110 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	8 kWh

MR16/GU10/PAR16

Product Data

Order product name	7MR16/F36 3000 DIM HO
Full product name	7MR16/F36 3000 DIM HO
Order code	929000263404
Material Nr. (12NC)	929000263404
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case

EAN/UPC - Product/Case	046677433659
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677433654


Dimensional drawing

Product	D	C
7MR16/F36 3000 DIM HO	50 mm	54 mm

Photometric data



Light Distribution Diagram - 7MR16/F36 3000 DIM HO



Spectral Power Distribution Colour - 7MR16/F36 3000 DIM HO

