



MASTER LEDtube EM/ Mains T8

MAS LEDtube 1500mm SO 20W 840 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.

Warnings and Safety

- -
- -

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	160 degree(s)
Luminous Flux	2,000 lm
Correlated Color Temperature (Nom)	4000 K
Color Consistency	<6
Color rendering index (CRI)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %


Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	20 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	Instant full light s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	No

MASTER LEDtube EM/Mains T8

Mechanical and Housing	
Product Length	1,500 mm
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Approval Marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	20 kWh
Product Data	
Order product name	MAS LEDtube 1500mm SO 20W 840 T8


Full product name	MAS LEDtube 1500mm SO 20W 840 T8
Full product code	871829173451200
Order code	929000287602
Material Nr. (12NC)	929000287602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291734512
Numerator - Packs per outer box	10
EAN/UPC - Case	8718291734529

Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS LEDtube 1500mm SO 20W 840 T8	25.68 mm	28 mm	1,500.0 mm	1,507.1 mm	1,514.2 mm

Photometric data



Light Distribution Diagram - MAS LEDtube 1500mm SO 20W 840 T8



Spectral Power Distribution Colour - MAS LEDtube 1500mm SO 20W 840 T8

MASTER LEDtube EM/Mains T8

