



LED PAR30 S/L

120V PAR30S 12.5W 15D 3000K 780 CW SOB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data


General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	50,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	15 degree(s)
Luminous Flux	780 lm
Luminous Intensity (Nom)	6,300 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	62.40 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	12.5 W
Lamp Current (Nom)	115 mA

Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	PAR30S [PAR 3.75 inch/95mm Short]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	13 kWh
Product Data	
Order product name	120V PAR30S 12.5W 15D 3000K 780 CW SOB
Full product name	120V PAR30S 12.5W 15D 3000K 780 CW SOB
Order code	929001110104
Material Nr. (12NC)	929001110104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677434939
Numerator - Packs per outer box	6

LED PAR30 S/L


EAN/UPC - Case	50046677434934
----------------	----------------

Dimensional drawing



Product	D	C
120V PAR30S 12.5W 15D 3000K 780 CW SOB	92 mm	93 mm

Photometric data



Light Distribution Diagram - 120V PAR30S 12.5W 15D 3000K 780 CW SOB

