



PAR38 LED

120V PAR38 17W 15D 3000K 1200 D AF SO

Philips PAR38 LED Single Optic Lamps with AirFlux Technology improves shopping experience with superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	17-100W
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	15 °
Luminous Flux (Nom)	1250 lm
Luminous Flux (Rated) (Nom)	1250 lm
Luminous Intensity (Nom)	10500 cd
Color Designation	White (WH)
Rated Beam Angle	15 °
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	74 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	17 W
Lamp Current (Nom)	167 mA


Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.85
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	89 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Suitable For Accent Lighting	Yes
Energy Certifications	Energy Star
Product Data	
Order product name	120V PAR38 17W 15D 3000K 1200 D AF SO
EAN/UPC - Product	046677435363
Order code	929001113204
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001113204
Net Weight (Piece)	0.001 kg

PAR38 LED

Warnings and Safety

- Suitable for use in damp locations.
- Not for use in totally enclosed luminaires.
- CAUTION: Risk of electric shock - do not use where directly exposed to water.
- NOTES: This device complies with Part 18 of the FCC rule. This product may cause interference with other devices. If interference occurs, change the location of the products involved. This RFLD device complies with Canadian ICES-005




Dimensional drawing



Par38 CL 120V 17W-120W 15D 3000K E26 D

Product	D	C
120V PAR38 17W 15D 3000K 1200 D AF SO	120.3 mm	130.5 mm

Photometric data



LEDspot, PAR38 12W 3000K 15D