



CorePro LEDcapsule LV

CorePro LEDcapsuleLV 1.2-10W 830 G4

The CorePro LEDcapsule is a true alternative to the halogen capsule. It is particularly suitable for task lighting and decorative applications in homes, shops, hotels and restaurants. Compatible with existing fixtures with G4 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers significant energy savings and minimises maintenance costs without any compromise on light quality.

Product data


General Information			
Cap-Base	G4 [G4]	Input Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Power Consumption	1.2 W
Switching Cycle	50,000	Lamp Current (Nom)	200 mA
Lighting Technology	LED	Wattage Equivalent	10 W
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.5
		Voltage (Nom)	12 V
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	No
Luminous Flux	105 lm		
Color Designation	White (WH)	Mechanical and Housing	
Correlated Color Temperature (Nom)	3000 K	Bulb Shape	Capsule
Luminous Efficacy (rated) (Nom)	87.5 lm/W		
Color Consistency	<6	Approval and Application	
Color rendering index (CRI)	80	Energy Consumption kWh/1000 h	2 kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Line Frequency	50 to 60 Hz		

CorePro LEDcapsule LV

Product Data	
Order product name	CorePro LEDcapsuleLV 1.2-10W 830 G4
Full product name	CorePro LEDcapsuleLV 1.2-10W 830 G4
Full product code	871869642228100
Order code	929001118702
Material Nr. (12NC)	929001118702


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696422281
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696422298

Dimensional drawing




Product	D	C
CorePro LEDcapsuleLV 1.2-10W 830 G4	14.3 mm	39.2 mm

Photometric data



Light Distribution Diagram - CorePro LEDcapsuleLV 1.2-10W 830 G4



Spectral Power Distribution Colour - CorePro LEDcapsuleLV 1.2-10W 830 G4

