



# MASTER LEDspot LV

## MAS LEDspotLV 3.5-20W 827 MR11 24D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

### Product data

General Information	
Cap-Base	GU4 [ GU4]
Nominal Lifetime (Nom)	40000 h
Switching Cycle	50000X
Technical Type	3.5-20W
Light Technical	
Colour Code	827 [ CCT of 2700K]
Beam Angle (Nom)	24 °
Light Distribution	- [ -]
Luminous Flux (Nom)	210 lm
Luminous Flux (Rated) (Nom)	210 lm
Luminous Intensity (Nom)	1000 cd
Colour Designation	Warm White (WW)
Rated Beam Angle	24 °
Colour Temperature, horizontal (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	60.00 lm/W

Color Consistency	<6
Colour Rendering Index horiz (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	200 lm
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	3.5 W
Lamp Current (Nom)	640 mA
Wattage Equivalent	20 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	instant full light
Power Factor (Nom)	0.5
Voltage (Nom)	12 V

# MASTER LEDspot LV

## Temperature

T-Case Maximum (Nom)	94 °C
----------------------	-------

## Controls and Dimming

Dimmable	No
----------	----

## Approval and Application

Energy Efficiency Label	A+
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh


## Product Data

Full product code	871869641019600
Order product name	MAS LEDspotLV 3.5-20W 827 MR11 24D
EAN/UPC - Product	8718696410196
Order code	41019600
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	929001123802
Net Weight (Piece)	0.024 kg

## Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights


## Dimensional drawing




LED 3.5-20W 827 MR11 24D

Product	D	C
MAS LEDspotLV 3.5-20W 827 MR11 24D	35 mm	40 mm

## Photometric data



3.5-20 W GU4 MR11 /827 24D



3.5-20 W GU4 MR11 /827 24D

## MASTER LEDspot LV

