



# MasterClass LEDtube InstantFit T8

10T8/48-3500 IF 10/1

The MasterClass InstantFit TLED is a great LED solution suitable for replacing T8 fluorescent lamps, using the existing ballast. MasterClass TLEDs feature a shatter-resistant polycarbonate construction, 70,000 hour life and a standard 7-year limited warranty. When maximum energy savings and long life are needed, Philips MasterClass TLED are the solution.

## Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	835 [CCT of 3500K]
Luminous Flux	1,500 lm
Correlated Color Temperature (Nom)	3500 K
Color Consistency	<6
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	10 W
Starting Time (Nom)	0.5 s


Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277, 347 V
Temperature	
Ambient temperature range	-4 °F to 113 °F
T-Case Maximum (Nom)	104 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	1,200 mm
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Approval Marks	UL certificate RoHS compliance DLC compliance
Energy Consumption kWh/1000 h	- kWh

MasterClass LEDtube InstantFit T8

Energy Certifications	DLC Standard
Product Data	
Order product name	10T8/48-3500 IF 10/1
Full product name	10T8/48-3500 IF 10/1
Order code	468272
Material Nr. (12NC)	929001124064


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677472207
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677468274

Dimensional drawing




Product	D1	D2	A1	A2	A3
10T8/48-3500 IF 10/1	1-1/16 inch	1-1/8 inch	47-3/16 inch	47-1/2 inch	47-3/4 inch

Photometric data



Spectral Power Distribution Colour - 10T8/48-3500 IF 10/1

General uniform lighting - 10T8/48-3500 IF 10/1



Light Distribution Diagram - 10T8/48-3500 IF 10/1

## MasterClass LEDtube InstantFit T8

