



T8

10T8/48-3500 IF 10/1 TAA/NAFTA

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.


Product data

General Information		Input Frequency	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	10 W
Nominal lifetime	50,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.9
EU RoHS compliant	Yes	Voltage (Nom)	120-277, 347 V
Light Technical		UL Type	Type A - works on ballast
Color Code	835 [CCT of 3500K]	Temperature	
Beam Angle (Nom)	180 degree(s)	Ambient temperature range	-20 °C to 45 °C
Luminous Flux	1,500 lm	T-Case Maximum (Nom)	40 °C
Color Designation	White (WH)	Controls and Dimming	
Correlated Color Temperature (Nom)	3500 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	150.00 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Material	Plastic
Color rendering index (CRI)	82	Product Length	1,200 mm
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	Tube, double-ended
Operating and Electrical			
Line Frequency	50 to 60 Hz		

Approval and Application	
Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance DLC compliance
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	DLC Standard
Product Data	
Order product name	10T8/48-3500 IF 10/1 TAA/NAFTA



Full product name	10T8/48-3500 IF 10/1 TAA/NAFTA
Order code	929001124084
Material Nr. (12NC)	929001124084
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677472610
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677469578

Dimensional drawing




Product	D1	D2	A1	A2	A3
10T8/48-3500 IF 10/1 TAA/NAFTA	25.68 mm	28 mm	1,198.0 mm	1,205.0 mm	1,212.0 mm

Photometric data




Spectral Power Distribution Colour - 10T8/48-3500 IF 10/1 TAA/NAFTA

General uniform lighting - 10T8/48-3500 IF 10/1 TAA/NAFTA




Light Distribution Diagram - 10T8/48-3500 IF 10/1 TAA/NAFTA

Lifetime



Lumen Maintenance Diagram - 10T8/48-3500 IF 10/1 TAA/NAFTA



Life Expectancy Diagram - 10T8/48-3500 IF 10/1 TAA/NAFTA

