



MASTER VALUE LEDspot LV

MAS LEDspotLV DimTone 6.5–35W MR16 36D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED

EU RoHS compliant	Yes
Light Technical	
Color Code	822-827 [tunable warm white]
Beam Angle (Nom)	36 degree(s)

MASTER VALUE LEDspot LV

Luminous Flux	410 lm
Luminous Intensity (Nom)	900 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	63.08 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	370 lm

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	6.5 W
Lamp Current (Nom)	800 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V

Temperature

T-Case Maximum (Nom)	80 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Shape	MR16 [2Inch/50mm]
------------	-------------------


Approval and Application

Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	7 kWh
EyeComfort	Yes

Product Data

Order product name	MAS LEDspotLV DimTone 6.5-35W MR16 36D
Full product name	MAS LEDspotLV DimTone 6.5-35W MR16 36D
Full product code	871869644215900
Order code	929001127902
Material Nr. (12NC)	929001127902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696442159
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696442166


Dimensional drawing




Product	D	C
MAS LEDspotLV DimTone 6.5-35W MR16 36D	51 mm	50 mm

MASTER VALUE LEDspot LV

Photometric data



Light Distribution Diagram - MAS LEDspotLV DimTone 6.5-35W MR16 36D



Spectral Power Distribution Colour - MAS LEDspotLV DimTone 6.5-35W MR16 36D

