



MASTER VALUE LEDspot MV

MAS LEDspotMV VLE D 4.3-50W GU10 840 25D

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiances for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings than normal LED spots.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap-Base	GU10 [GU10]
Nominal lifetime	35,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	420 lm

Luminous Intensity (Nom)	1,400 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	90.70 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	390 lm
Operating and Electrical	
Line Frequency	50 to 60 Hz

MASTER VALUE LEDspot MV

Input Frequency	50 to 60 Hz
Power Consumption	4.3 W
Lamp Current (Nom)	23 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	83 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Shape	PAR16 [PAR 2 inch/50mm]
------------	-------------------------

Approval and Application

Suitable For Accent Lighting	Yes
------------------------------	-----

Energy Consumption kWh/1000 h	5 kWh
EyeComfort	Yes


Product Data

Order product name	MAS LEDspotMV VLE D 4.3-50W GU10 840 25D
Full product name	MAS LEDspotMV VLE D 4.3-50W GU10 840 25D
Full product code	871869643846600
Order code	929001130302
Material Nr. (12NC)	929001130302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696438466
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696438473


Dimensional drawing

Product	D	C
MAS LEDspotMV VLE D 4.3-50W GU10 840 25D	50 mm	55 mm

Photometric data



Light Distribution Diagram - MAS LEDspotMV VLE D 4.3-50W GU10 840 25D



Spectral Power Distribution Colour - MAS LEDspotMV VLE D 4.3-50W GU10 840 25D

MASTER VALUE LEDspot MV

