



# CorePro LEDcapsule LV

## CorePro LEDcapsuleLV 2-20W 830 G4

The CorePro LEDcapsule is a true alternative to the halogen capsule. It is particularly suitable for task lighting and decorative applications in homes, shops, hotels and restaurants. Compatible with existing fixtures with G4 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers significant energy savings and minimises maintenance costs without any compromise on light quality.

### Product data

General Information	
Cap-Base	G4 [G4]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	200 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	2 W
Lamp Current (Nom)	290 mA
Wattage Equivalent	20 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	12 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	Capsule
Approval and Application	
Energy Consumption kWh/1000 h	3 kWh

## CorePro LEDcapsule LV

### Product Data

Order product name	CorePro LEDcapsuleLV 2-20W 830 G4
Full product name	CorePro LEDcapsuleLV 2-20W 830 G4
Full product code	871869641916800
Order code	929001131802
Material Nr. (12NC)	929001131802

### Numerator - Quantity Per Pack

1

### EAN/UPC - Product/Case

8718696419168


### Numerator - Packs per outer box

12

### EAN/UPC - Case



8718696419175

### Dimensional drawing



Product	D	C
CorePro LEDcapsuleLV 2-20W 830 G4	14.3 mm	45 mm

### Photometric data



Light Distribution Diagram - CorePro LEDcapsuleLV 2-20W 830 G4

Spectral Power Distribution Colour - CorePro LEDcapsuleLV 2-20W 830 G4

