



CorePro LEDcapsule LV

CorePro LEDcapsuleLV 2-20W 830 G4

The CorePro LEDcapsule is a true alternative to the halogen capsule. It is particularly suitable for task lighting and decorative applications in homes, shops, hotels and restaurants. Compatible with existing fixtures with G4 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers huge energy savings and minimizes maintenance costs without any compromise on light quality.

Product data

General Information	
Cap-Base	G4 [G4]
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	2-20W

Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux (Nom)	200 lm
Luminous Flux (Rated) (Nom)	200 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	2 W

Lamp Current (Nom)	290 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	No


Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Consumption kWh/1000 h	3 kWh

Product Data	
Full product code	871869641916800
Order product name	CorePro LEDcapsuleLV 2-20W 830 G4
EAN/UPC - Product	8718696419168
Order code	929001131802
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12

CorePro LEDcapsule LV

Material Nr. (12NC)	929001131802
Net Weight (Piece)	0.008 kg


Dimensional drawing




LED 2-20W 830 G4

Product	D	C
CorePro LEDcapsuleLV 2-20W 830 G4	14.3 mm	45 mm

Photometric data



2-20 W G4 /830



G4 /830

