



LED PAR30 S/L

120V PAR30L 12.7W 35D 3000K 900 D SO

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	35 degree(s)
Luminous Flux	900 lm
Luminous Intensity (Nom)	2,400 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	71 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	12.7 W
Lamp Current (Nom)	125 mA


Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.85
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	89 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	PAR30L [PAR 3.75 inch/95mm Long]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Certifications	Energy Star
Product Data	
Order product name	120V PAR30L 12.7W 35D 3000K 900 D SO
Full product name	120V PAR30L 12.7W 35D 3000K 900 D SO
Order code	929001132704
Material Nr. (12NC)	929001132704

LED PAR30 S/L

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677454708
Numerator - Packs per outer box	6


EAN/UPC - Case	50046677454703
----------------	----------------

Dimensional drawing




Product	D	C
120V PAR30L 12.7W 35D 3000K 900 D SO	92 mm	116 mm

Photometric data




Spectral Power Distribution Colour - 120V PAR30L 12.7W 35D 3000K 900 D SO



CalcLux Photometrics 4.5 Philips Lighting B.V. Page 1/1

General uniform lighting - 120V PAR30L 12.7W 35D 3000K 900 D SO



Light Distribution Diagram - 120V PAR30L 12.7W 35D 3000K 900 D SO

LED PAR30 S/L

