



MASTER LED candles and lusters

MAS LEDlustre DT 4-25W E14 P48 CL

Delivering incandescent-like sparkling light effects, MASTER LED candles and lusters are ideal for general and decorative lighting in the hospitality industry as well as in home environments. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass candles and lusters fit all existing fixtures with an E14, B15, B22 or E27 socket, and enhance the aesthetic appeal of the chandelier or luminaire both when on and off, with their unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost.

Product data

General Information		Operating and Electrical	
Cap-Base	E14 [E14]	Input Frequency	50 to 60 Hz
Nominal Lifetime (Nom)	25000 h	Power (Rated) (Nom)	4 W
Switching Cycle	50000X	Lamp Current (Nom)	25 mA
Technical Type	4-25W	Starting Time (Nom)	0.5 s
		Warm Up Time to 60% Light (Nom)	instant full light
		Power Factor (Nom)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	822-827 [tunable warm white]	T-Case Maximum (Nom)	85 °C
Luminous Flux (Nom)	250 lm		
Luminous Flux (Rated) (Nom)	250 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	Yes
Correlated Color Temperature (Nom)	2200-2700 K		
Luminous Efficacy (rated) (Nom)	65 lm/W		
Color Consistency	<6		
Color Rendering Index (Nom)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %		

MASTER LED candles and lusters

Mechanical and Housing

Bulb Finish Clear

Approval and Application

Energy Efficiency Label (EEL) A+

Suitable For Accent Lighting No

Energy Consumption kWh/1000 h 4 kWh

Product Data

Full product code 871869645378000

Order product name MAS LEDlustre DT 4-25W E14 P48 CL

EAN/UPC - Product 8718696453780

Order code 929001140002


Numerator - Quantity Per Pack 1

Numerator - Packs per outer box 10

Material Nr. (12NC) 929001140002

Net Weight (Piece) 0.072 kg


Dimensional drawing




LED DT 4-25W E14 P48 CL

Product	D	C
MAS LEDlustre DT 4-25W E14 P48 CL	48 mm	95 mm

Photometric data



DT 4-25W E14 P48 CL 250lm



Lightcolor /827

MASTER LED candles and lusters

