



MASTER VALUE LEDs

pot LV

MASTER LEDspotLV VLE 3.4-20W 830 MR16 24D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights


Product data

General Information			
Cap-Base	GU5.3 [GU5.3]	Beam Angle (Nom)	24 degree(s)
Nominal lifetime	25,000 hour(s)	Luminous Flux	240 lm
Switching Cycle	50,000	Luminous Intensity (Nom)	1,000 cd
Lighting Technology	LED	Color Designation	White (WH)
EU RoHS compliant	Yes	Correlated Color Temperature (Nom)	3000 K
		Luminous Efficacy (rated) (Nom)	65.00 lm/W
		Color Consistency	<6
		Color rendering index (CRI)	80
		LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical			
Color Code	830 [CCT of 3000K]		


MASTER VALUE LEDspot LV

Luminous Flux in 90° Cone (Rated)	225 lm
Operating and Electrical	
Power Consumption	3.4 W
Lamp Current (Nom)	520 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]

Dimensional drawing




Photometric data



Light Distribution Diagram - MAS LEDspotLV VLE 3.4-20W 830 MR16 24D

Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh
Product Data	
Order product name	MAS LEDspotLV VLE 3.4-20W 830 MR16 24D
Full product name	MASTER LEDspotLV VLE 3.4-20W 830 MR16 24D
Full product code	871869647576800
Order code	47576800
Material Nr. (12NC)	929001147702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696475768
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696475775

Product	D	C
MAS LEDspotLV VLE 3.4-20W 830 MR16 24D	50 mm	49 mm



Spectral Power Distribution Colour - MAS LEDspotLV VLE 3.4-20W 830 MR16 24D

MASTER VALUE LEDspot LV

