

PHILIPS

Eco passport

MAS LEDspotLV VLE D6.3-35W 830MR16 36DRN MASTER LEDspot LV

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.



Our Eco passport



Energy

- Dimmable: Yes
- Energy efficiency label (EEL): A
- Luminous efficacy (rated) (nom.): 63 lm/W
- Power (Rated) (Nom): 6.3 W




Circularity

- Nominal lifetime (nom.): 25000 h



Packaging

- SAP Weight Paper Unit (Case): 0.160 kg
- SAP Weight Paper Unit (Piece): 0.007 kg



Substances

- EU RoHS compliant: No



Weight & Materials

- Net weight (piece): 0.045 kg

Energy efficiency ranking / External awards

