



MASTER VALUE LEDs

pot LV

MASTER LEDspotLV D 7-35W 927 MR16 36D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data


General Information			
Cap-Base	GU5.3 [GU5.3]	Beam Angle (Nom)	36 degree(s)
Nominal lifetime	40,000 hour(s)	Luminous Flux	400 lm
Switching Cycle	50,000	Luminous Intensity (Nom)	1,150 cd
Lighting Technology	LED	Color Designation	Warm White (WW)
EU RoHS compliant	Yes	Correlated Color Temperature (Nom)	2700 K
		Luminous Efficacy (rated) (Nom)	57.14 lm/W
		Color Consistency	<6
		Color rendering index (CRI)	90
		LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical			
Color Code	927		

MASTER VALUE LEDspot LV

Luminous Flux in 90° Cone (Rated)	400 lm
Operating and Electrical	
Power Consumption	7 W
Lamp Current (Nom)	720 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	92 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]


Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	8 kWh
EyeComfort	Yes
Product Data	
Order product name	MAS LEDspotLV D 7-35W 927 MR16 36D
Full product name	MASTER LEDspotLV D 7-35W 927 MR16 36D
Full product code	871869665925000
Order code	65925000
Material Nr. (12NC)	929001153132
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696659250
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696659267

Dimensional drawing




Product	D	C
MAS LEDspotLV D 7-35W 927 MR16 36D	51 mm	51 mm

Photometric data




Spectral Power Distribution Colour - MAS LEDspotLV D 7-35W 927 MR16 36D



Light Distribution Diagram - MAS LEDspotLV D 7-35W 927 MR16 36D

MASTER VALUE LEDspot LV

Photometric data



CatLight Pro 4.5 Philips Lighting B.V. Page 3/7

General uniform lighting - MAS LEDspotLV D 7-35W 927 MR16 36D

