



BR/R LED

9BR30/LED/827-22/DIM 120V 6/1

Philips Dimmable LED Reflector Lamps provide a soft, diffused level of light and smooth dimming to reduce glare. The sleek, lightweight design is ideal for downlighting.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
RoHS mark	RoHS mark
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	9-65W

Light Technical	
Color Code	822-827 [tunable warm white]
Initial lumen (Nom)	650 lm
Luminous Flux (Rated) (Nom)	650 lm
Color Designation	Soft White
Correlated Color Temperature (Nom)	2200-2700 K
Luminous Efficacy (rated) (Nom)	73 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	9 W
Lamp Current (Nom)	92 mA
Wattage Equivalent	65 W
Starting Time (Nom)	0.5 s

Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.8
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	76 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted (FR)


Approval and Application	
Energy star mark	Energy star
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	9 kWh

Product Data	
Order product name	9BR30/LED/827-22/DIM 120V
EAN/UPC - Product	046677457044
Order code	457044
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

BR/R LED

Material Nr. (12NC)	929001155504
Net Weight (Piece)	0.094 kg



Dimensional drawing



BR30 G5 120V 9W-65W 650lm 2700K E26 D

Product	D	C
9BR30/LED/827-22/DIM 120V	96 mm	132 mm

Photometric data



LEDbulb, Basic BR30 9W-65W 2700K 650lm WG

