



LED BR30

8BR30/LED/850/DIM 120V 6/1

8BR30/LED/850/DIM 120V

Philips BR30 LED lamps are the smart alternative to standard incandescent. The traditional lamp design can provide excellent dimming performance with spectacular energy savings. They provide the beautiful light and dependable performance you expect from LED at an economical price.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
RoHS mark	RoHS mark
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	8-65W
Light Technical	
Color Code	850 [CCT of 5000K]
Initial lumen (Nom)	650 lm
Luminous Flux (Rated) (Nom)	650 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	82 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz


Power (Rated) (Nom)	8 W
Lamp Current (Nom)	82 mA
Wattage Equivalent	65 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.8
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	76 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted (FR)
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	8 kWh

LED BR30

Energy Certifications	Energy Star
Product Data	
Order product name	8BR30/LED/850/DIM 120V
EAN/UPC - Product	046677458065
Order code	458067

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001155604
Net Weight (Piece)	0.094 kg



Dimensional drawing




BR30 G5 120V 8.0W-65W 650lm 5000K E26 D

Product	D	C
8BR30/LED/850/DIM 120V	96 mm	132 mm

Photometric data



LEDbulb, AmbientLED BR30 9W-65W 5000K 650lm



LED BR30

