



# CorePro LEDspot MV

## CorePro LEDspotMV 3.5-35W GU10 827 36DRS

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. These GU10 LED spot lights are compatible with most existing fixtures with a GU10 LED base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots deliver significant energy savings and minimize maintenance costs.

### Product data


General Information		Input Frequency	
Cap-Base	GU10 [GU10]	Input Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Power Consumption	3.5 W
Switching Cycle	50,000	Lamp Current (Nom)	30 mA
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	instant full light s
		Power Factor (Fraction)	0.5
		Voltage (Nom)	220-240 V
Light Technical		Controls and Dimming	
Color Code	827 [CCT of 2700K]	Dimmable	No
Beam Angle (Nom)	36 degree(s)		
Luminous Flux	280 lm	Mechanical and Housing	
Luminous Intensity (Nom)	650 cd	Bulb Finish	White
Color Designation	White (WH)	Bulb Shape	MR16 [2inch/50mm]
Correlated Color Temperature (Nom)	2700 K		
Luminous Efficacy (rated) (Nom)	71 lm/W	Approval and Application	
Color Consistency	<6	Suitable For Accent Lighting	Yes
Color rendering index (CRI)	80	Energy Consumption kWh/1000 h	4 kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Luminous Flux in 90° Cone (Rated)	250 lm	Product Data	
		Order product name	CorePro LEDspotMV 3.5-35W GU10 827 36DRS
		Full product name	CorePro LEDspotMV 3.5-35W GU10 827 36DRS
Operating and Electrical			
Line Frequency	50 to 60 Hz		

# CorePro LEDspot MV

Full product code	871829179916000
Order code	929001156662
Material Nr. (12NC)	929001156662
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291799160



Numerator - Packs per outer box	10
EAN/UPC - Case	8718291799177

## Dimensional drawing



Product	D	C
CorePro LEDspotMV 3.5-35W GU10 827 36DRS	50 mm	55 mm

## Photometric data



Light Distribution Diagram - CorePro LEDspotMV 3.5-35W GU10 827 36DRS

Spectral Power Distribution Colour - CorePro LEDspotMV 3.5-35W GU10 827 36DRS

