



CorePro LEDcandle

CorePro lustre ND 4-25W E27 827 P45 FR

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data

| General Information | |
|--|-----------------------|
| Cap base | E27 [E27] |
| Nominal lifetime (nom.) | 15000 h |
| Switching cycle | 50000X |
| Technical type | 4-25W |
| Light Technical | |
| Colour code | 827 [CCT of 2,700 K] |
| Luminous flux (nom.) | 250 lm |
| Luminous flux (rated) (nom.) | 250 lm |
| Colour designation | Warm white (WW) |
| Correlated colour temperature (nom.) | 2700 K |
| Luminous efficacy (rated) (nom.) | 62.50 lm/W |
| Colour consistency | <6 |
| Color rendering index (nom.) | 80 |
| LLMF at end of nominal lifetime (nom.) | 70 % |
| Operating and Electrical | |
| Input frequency | 50 to 60 Hz |
| Power (Rated) (Nom) | 4 W |
| Lamp current (nom.) | 35 mA |
| Wattage equivalent | 25 W |
| Starting time (nom.) | 0.5 s |


| Warm-up time to 60% light (nom.) | 0.5 s |
|----------------------------------|--|
| Power factor (nom.) | 0.4 |
| Voltage (Nom) | 220-240 V |
| Temperature | |
| T-Case maximum (nom.) | 75 °C |
| Controls and Dimming | |
| Dimmable | no |
| Mechanical and Housing | |
| Bulb finish | Frosted (FR) |
| Approval and Application | |
| Energy efficiency label (EEL) | A+ |
| Energy Consumption kWh/1000 h | 4 kWh |
| Product Data | |
| Full product code | 871829178705100 |
| Order product name | CorePro lustre ND 4-25W E27 827 P45 FR |
| EAN/UPC – product | 8718291787051 |
| Order code | 78705100 |
| Local Code | CPL4E27827FR |

CorePro LEDcandle

| | |
|---------------------------------|--------------|
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 10 |
| Material no. (12NC) | 929001157602 |

| | |
|--------------------|----------|
| Net weight (piece) | 0.040 kg |
|--------------------|----------|



Dimensional drawing




LED ND 4-25W E27 827 220-240V P45 FR

| Product | D | C |
|--|-------|-------|
| CorePro lustre ND 4-25W E27 827 P45 FR | 45 mm | 87 mm |

Photometric data



CorePro LEDlustre 4-25W E27 827 FR P45




CorePro LEDcandle

Lifetime



LEDbulb 60W E14 827 FR B38



LEDbulb 60W E14 827 FR B38

