



T8

14T8/48-4000 IF 10/1 DIM TAA/NAFTA

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data

General information		Wattage Equivalent	
Base	G13 [Medium Bi-Pin Fluorescent]		32 W
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
Nominal Lifetime (Nom)	50000 h	Warm Up Time to 60% Light (Nom)	0.5 s
Switching Cycle	50000X	UL Type	Type A - works on ballast
		Power Factor (Nom)	0.9
		Voltage (Nom)	120-277, 347 V
Light technical		Temperature	
Color Code	841 [CCT of 4100K (841)]	T-Ambient (Max)	45 °C
Beam Angle (Nom)	180 °	T-Ambient (Min)	-20 °C
Initial lumen (Nom)	2100 lm	T-Storage (Max)	65 °C
Color Designation	Cool White (CW)	T-Storage (Min)	-40 °C
Correlated Color Temperature (Nom)	4000 K	T-Case Maximum (Nom)	45 °C
Luminous Efficacy (rated) (Nom)	150.00 lm/W		
Color Consistency	<6	Controls and dimming	
Color Rendering Index (Nom)	82	Dimmable	Yes
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and electrical		Mechanical and housing	
Input Frequency	50 to 60 Hz	Bulb Finish	Frosted
Power (Rated) (Nom)	14 W	Bulb Material	Plastic

T8


Product Length	48 in
Bulb Shape	Tube, double-ended
Approval and application	
Energy Saving Product	Yes
Approbation Marks	UL certificate RoHS compliance DLC compliance
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	DLC Standard

Product data

Order product name	14T8/48-4000 IF 10/1 DIM TAA/NAFTA
--------------------	------------------------------------

EAN/UPC - Product	046677472665
Order code	469627
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001158784
Net Weight (Piece)	0.001 kg
Model Number	9290011587C


Dimensional drawing



14T8/48-4000 IF 10/1 DIM TAA/NAFTA

Product	D1	D2	A1	A2	A3
14T8/48-4000 IF 10/1 DIM TAA/NAFTA	25.7 mm	28 mm	1198.0 mm	1205.0 mm	1212.0 mm

Photometric data



LEDtube 1200mm 15W G13 T8 840 2100lm

LEDtube 1200mm 15W G13 T8 840 2100lm


T8

Photometric data




LEDtube 1200mm 15W G13 T8 840 2100lm

Lifetime



LEDtube HF 1500mm 26W G5 T5



LEDtube 1200mm 14-32W G13

