



# Standard LED candles & lusters

## LEDBulb 4-40W E27 3000K 220V P45 2BC

Standard LED candles are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving candles. They deliver huge energy savings and minimize maintenance costs. The Standard LED candle is the perfect candle for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

### Product data


| General Information                   |                    | Operating and Electrical  |             |
|---------------------------------------|--------------------|---------------------------|-------------|
| Cap-Base                              | E27 [E27]          | Line Frequency            | 50 to 60 Hz |
| Nominal lifetime                      | 15,000 hour(s)     | Input Frequency           | 50 to 60 Hz |
| Switching Cycle                       | 50,000             | Power Consumption         | 4 W         |
| Lighting Technology                   | LED                | Lamp Current (Nom)        | 40 mA       |
| EU RoHS compliant                     | Yes                | Wattage Equivalent        | 40 W        |
| Light Technical                       |                    | Starting Time (Nom)       | 0.5 s       |
| Color Code                            | 830 [CCT of 3000K] | Warm-up time to 60% light | 0.5 s       |
| Beam Angle (Nom)                      | 150 degree(s)      | Power Factor (Fraction)   | 0.5         |
| Luminous Flux                         | 350 lm             | Voltage (Nom)             | 220-240 V   |
| Color Designation                     | White (WH)         | Temperature               |             |
| Correlated Color Temperature (Nom)    | 3000 K             | T-Case Maximum (Nom)      | 90 °C       |
| Luminous Efficacy (rated) (Nom)       | 87.00 lm/W         | Controls and Dimming      |             |
| Color Consistency                     | <6                 | Dimmable                  | No          |
| Color rendering index (CRI)           | 80                 | Mechanical and Housing    |             |
| LLMF At End Of Nominal Lifetime (Nom) | 70 %               | Bulb Finish               | Frosted     |

Standard LED candles & lusters

|                               |                                      |
|-------------------------------|--------------------------------------|
| Bulb Shape                    | P45 [P 45mm]                         |
| Approval and Application      |                                      |
| Energy Consumption kWh/1000 h | - kWh                                |
| Product Data                  |                                      |
| Order product name            | LEDBulb 4-40W E27 3000K 220V P45 2BC |
| Full product name             | LEDBulb 4-40W E27 3000K 220V P45 2BC |
| Full product code             | 871869678890500                      |



|                                 |               |
|---------------------------------|---------------|
| Order code                      | 929001160991  |
| Material Nr. (12NC)             | 929001160991  |
| Numerator - Quantity Per Pack   | 1             |
| EAN/UPC - Product/Case          | 8718696788905 |
| Numerator - Packs per outer box | 6             |
| EAN/UPC - Case                  | 8718696788912 |

Dimensional drawing




| Product                              | D     | C     |
|--------------------------------------|-------|-------|
| LEDBulb 4-40W E27 3000K 220V P45 2BC | 45 mm | 87 mm |

Photometric data



Spectral Power Distribution Colour - LEDBulb 4-40W E27 3000K 220V P45 2BC

General uniform lighting - LEDBulb 4-40W E27 3000K 220V P45 2BC



Light Distribution Diagram - LEDBulb 4-40W E27 3000K 220V P45 2BC

## Standard LED candles & lusters

