



# Standard LED bulbs

## LEDBulb 6-50W E27 830 220-240V 1PF/10

Standard LED bulbs are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving bulbs. They deliver huge energy savings and minimize maintenance costs. The Standard LED bulb is the perfect bulb for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

### Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	470 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	78.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	6 W


Lamp Current (Nom)		55 mA
Wattage Equivalent		50 W
Starting Time (Nom)		0.5 s
Warm-up time to 60% light		0.5 s
Power Factor (Fraction)		0.5
Voltage (Nom)		220-240 V
Temperature		
T-Case Maximum (Nom)		75 °C
Controls and Dimming		
Dimmable		No
Mechanical and Housing		
Bulb Finish		Frosted
Bulb Shape		A60 [A 60mm]
Approval and Application		
Energy Consumption kWh/1000 h		6 kWh
Product Data		
Order product name		LEDBulb 6-50W E27 830 220-240V 1PF/10

Standard LED bulbs

Full product name	LEDBulb 6-50W E27 830 220-240V 1PF/10
Full product code	871869665806200
Order code	929001162011
Material Nr. (12NC)	929001162011
Numerator - Quantity Per Pack	1



EAN/UPC - Product/Case	8718696658062
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696658079

Dimensional drawing



Product	D	C
LEDBulb 6-50W E27 830 220-240V 1PF/10	60 mm	110 mm

Photometric data



Light Distribution Diagram - LEDBulb 6-50W E27 830 220-240V 1PF/10

Spectral Power Distribution Colour - LEDBulb 6-50W E27 830 220-240V 1PF/10

