



# CorePro LEDbulb

## CorePro LEDbulb ND 5.5-40W A60 E27 830

CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings and minimize maintenance cost.

### Product data

General Information	
Cap base	E27 [ E27]
Nominal lifetime (nom.)	15000 h
Switching cycle	50000X
Technical type	5.5-40W

Light Technical	
Colour code	830 [ CCT of 3,000 K]
Beam Angle (Nom)	200 °
Luminous flux (nom.)	470 lm
Luminous flux (rated) (nom.)	470 lm
Colour designation	White (WH)
Correlated colour temperature (nom.)	3000 K
Luminous efficacy (rated) (nom.)	85.45 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	5.5 W
Lamp current (nom.)	55 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s

Power factor (nom.)	0.5
Voltage (Nom)	220-240 V

Temperature	
T-Case maximum (nom.)	84 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb finish	Frosted (FR)


Approval and Application	
Energy efficiency label (EEL)	A+
Energy-saving product	Yes
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	6 kWh

Product Data	
Full product code	871869657993000
Order product name	CorePro LEDbulb ND 5.5-40W A60 E27 830
EAN/UPC – product	8718696579930
Order code	57993000
Numerator – quantity per pack	1

# CorePro LEDbulb

Numerator – packs per outer box	10
Material no. (12NC)	929001162032
Net weight (piece)	0.076 kg

## Dimensional drawing



LED 6-40W E27 830

Product	D	C
CorePro LEDbulb ND 5.5-40W A60 E27 830	60 mm	110 mm

## Photometric data

