



LEDLamps

LEDBulb 9.5-60W E27 3000K 230V A60 AU/PF

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime (nom.)	15000 h
Switching cycle	50000X
Technical type	8-60W
Light Technical	
Colour code	830 [CCT of 3,000 K]
Beam Angle (Nom)	200 °
Luminous flux (nom.)	806 lm
Luminous flux (rated) (nom.)	806 lm
Colour designation	White (WH)
Correlated colour temperature (nom.)	3000 K
Luminous efficacy (rated) (nom.)	100.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	8 W
Lamp current (nom.)	75 mA
Starting time (nom.)	0.5 s


Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	86 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb finish	Frosted (FR)
Approval and Application	
Energy efficiency label (EEL)	A+
Energy-saving product	Yes
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	8 kWh
Product Data	
Full product code	871869648202500
Order product name	LEDBulb 9.5-60W E27 3000K 230V A60 AU/PF
EAN/UPC – product	8718696482025

LEDLamps

Order code	48202500
Numerator – quantity per pack	1
Numerator – packs per outer box	12
Material no. (12NC)	929001162219

Net weight (piece)	0.076 kg
--------------------	----------

Dimensional drawing



LED 9.5-60W E27 830

Product	D	C
LEDBulb 9.5-60W E27 3000K 230V A60 AU/PF	60 mm	110 mm

Photometric data

