



Standard LED bulbs

Standard LEDBulb 9.5-70W E27 830 220-240V 2BL/4

Standard LED bulbs are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving bulbs. They deliver huge energy savings and minimize maintenance costs. The Standard LED bulb is the perfect bulb for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

Product data


General Information			
Cap-Base	E27 [E27]	Power Consumption	9.5 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	75 mA
Switching Cycle	50,000	Wattage Equivalent	70 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.5
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	80 °C
Beam Angle (Nom)	150 degree(s)		
Luminous Flux	806 lm	Controls and Dimming	
Color Designation	White (WH)	Dimmable	No
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	84.00 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Frosted
Color rendering index (CRI)	80	Bulb Shape	A60 [A 60mm]
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical		Approval and Application	
Line Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	10 kWh
Input Frequency	50 to 60 Hz		

Standard LED bulbs

Product Data	
Order product name	LEDBulb 9.5-70W E27 830 220-240V 2BL/4
Full product name	Standard LEDBulb 9.5-70W E27 830 220-240V 2BL/4
Full product code	871869654574400
Order code	54574400
Material Nr. (12NC)	929001162241


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696545744
Numerator - Packs per outer box	4
EAN/UPC - Case	8718696545751

Dimensional drawing




Product	D	C
LEDBulb 9.5-70W E27 830 220-240V 2BL/4	60 mm	110 mm

Photometric data



Light Distribution Diagram - LEDBulb 9.5-70W E27 830 220-240V 2BL/4



Spectral Power Distribution Colour - LEDBulb 9.5-70W E27 830 220-240V 2BL/4

