



Standard LED bulbs

Standard LEDBulb 9.5-70W E27 3000K 220-240V 1BC

Standard LED bulbs are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving bulbs. They deliver huge energy savings and minimize maintenance costs. The Standard LED bulb is the perfect bulb for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

Product data


General Information		Power Consumption	
Cap-Base	E27 [E27]	Lamp Current (Nom)	75 mA
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.5
EU RoHS compliant	Yes	Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	80 °C
Beam Angle (Nom)	150 degree(s)	Controls and Dimming	
Luminous Flux	806 lm	Dimmable	No
Color Designation	White (WH)	Mechanical and Housing	
Correlated Color Temperature (Nom)	3000 K	Bulb Finish	Frosted
Luminous Efficacy (rated) (Nom)	84.00 lm/W	Bulb Shape	A60 [A 60mm]
Color Consistency	<6	Approval and Application	
Color rendering index (CRI)	80	Energy Consumption kWh/1000 h	10 kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

Standard LED bulbs

Product Data	
Order product name	LEDBulb 9.5-70W E27 830 220-240V 1BL/4
Full product name	Standard LEDBulb 9.5-70W E27 3000K 220-240V 1BC
Full product code	871869654558400
Order code	54558400
Material Nr. (12NC)	929001162271


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696545584
Numerator - Packs per outer box	4
EAN/UPC - Case	8718696545591

Dimensional drawing




Product	D	C
LEDBulb 9.5-70W E27 830 220-240V 1BL/4	60 mm	110 mm

Photometric data



Light Distribution Diagram - LEDBulb 9.5-70W E27 830 220-240V 1BL/4



Spectral Power Distribution Colour - LEDBulb 9.5-70W E27 830 220-240V 1BL/4

